

Assembly instructions

The specified connection dimensions refer to the metric DN 50 (diameter nominal) plug-in sockets prepared on site.

The assembly time for each urinal is approximately 20 minutes (weight approx. 18 kg). After assembly, a leak test must be carried out! Then insert the siphon cartridge.

Scope of delivery:

Urinal bowl, fastening kit (M10 x 120 mm)


Subject to technical changes.



 CleanPlus Finish



Rim height	User group	Middle of sewage pipe to finished floor
520 mm	Children aged 8 to 10	285 mm
570 mm	Children aged 11 to 14	335 mm
650 mm	From 15 years and adults	415 mm



Commissioning test after assembly

